



YRB32U29, Compression Splice Reducer, Barrel A 400 kcmil, Barrel B 250 kcmil, AL9CU

By Burndy

Catalog # [YRB32U29](#)

Aluminum Tin Plated Splice Reducer, Barrel A 400 kcmil, Barrel B 250 kcmil, AL9CU

Features

- Aluminum splice reducers are dual rated to accommodate both copper and aluminum wire
- Barrel features an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the wire strands during insertion
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with crimp location bands
- Factory pre-filled with PENETROX™ Type A13 oxide inhibitor
- Color coded end caps are factory inserted in the barrels to match the die color code and prevent foreign materials from entering the barrel

Application

Wire Reducing Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size B	250
Conductor - Copper Str Run	400 KCMIL
Conductor - Material	ALUMINUM / COPPER
Conductor - AL Str Size A	400
Conductor - AL Str Size B	250
Conductor - AL Str Size A	400
Range	
Conductor - AL Str Run	400 KCMIL
Conductor - AL Str Size B	250
Range	
Conductor - AL Str Tap	250 KCMIL
Conductor Type	CODE
Conductor - Copper Str Size	400



Conductor - Copper Str Size B	250
Range	
Conductor - Copper Str Tap	250 KCMIL

Configuration

Connector Type	DUAL RATED
----------------	------------

Current

Voltage - Maximum	35000
-------------------	-------

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	2-1/8 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	130 mm
mm	
Dimension - B Length inch	2.11 in
Dimension - Outside Diameter	1.31 in
inch	
Dimension - Length Overall	5.12 in
inch	
Dimension - Strip Length inch	2-3/16

General

Plated	Y
Color Code	Pink
Trade Name	HYREDUCER™
Die Index	300
UPC	781810243268
Material	Aluminum
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810243268
UPC 14 Digit GTIN	00781810243268

Logistics

Minimum Pack Quantity	20
Pallet Quantity	3600
Carton Quantity	20

Operational

Temperature Rating	194
--------------------	-----



A Hubbell brand