



YRB3428TTN, Copper - Compression Reducer



By Burndy
Catalog # [YRB3428TTN](#)

HYREDUCER™, Tin plated, 4.50 in long

Features

- Copper Compression Reducer Splice
- Tin Plated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	500 kcmil
Conductor - Copper Str Size B	4/O AWG

Configuration

Connector Type	• Reducer • Splice
----------------	--

Dimensions

Dimension - B Length inch	1.73 in
---------------------------	---------

Dimension - Outside Diameter	1.06 in
Dimension - Length BB inch	1.73 in
Dimension - Length Overall	4.50 in

General

Plated	Y
Color Code	Brown
Trade Name	HYREDUCER™
Die Index	• 20 • 299
UPC	781810278994
Material	Copper
Plating Type	Tin Plated
UPC 14 Digit GTIN	00781810278994

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1850
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)