



YRB3431TW, Copper - Compression Reducer



By Burndy
Catalog # [YRB3431TW](#)

HYREDUCER™, Hot Tin dipped, 500-350 kcmil, 4.50 in long

Features

- Copper Compression Reducer Splice
- Hot Tin Dipped

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	500 kcmil
Conductor - Copper Str Size B	350 kcmil

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.73 in

Dimension - Outside Diameter	1.06 in
Dimension - Length BB inch	1.73 in
Dimension - Length Overall	4.50 in

General

Color Code	Brown
Trade Name	HYREDUCER™
Die Index	• 20 • 299
UPC	781810192870
Material	Copper
Plating Type	Tin - Hot Dipped
UPC 14 Digit GTIN	00781810192870

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3700
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)