



YRB3432T, Copper HYREDUCER Splice

By Burndy
Catalog # [YRB3432T](#)



HYREDUCER™, 500-400 kcmil, 4.50 in long

Features

- Copper Compression Reducer Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Size A	500 kcmil
Conductor - Copper Str Size B	400 kcmil

Dimensions

Dimension - B Length inch	1.73 in
Dimension - Outside Diameter inch	1.06 in

Dimension - Length BB inch	1.73 in
Dimension - Length Overall inch	4.50 in

General

Color Code	Brown
Trade Name	HYREDUCER™
Die Index	20 299
UPC	781810367902
Material	Copper
UPC 14 Digit GTIN	00781810367902

Logistics

Minimum Pack Quantity	5
Pallet Quantity	7400
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)