



YRB3432TTN, Copper HYREDUCER Splice, Tin Plated



By Burndy
Catalog # [YRB3432TTN](#)

HYREDUCER™, Tin plated, 500-400 kcmil, 4.50 in long

Features

- Copper Compression Reducer Splice
- Tin Plated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	500 kcmil
Conductor - Copper Str Size B	400 kcmil

Dimensions

Dimension - B Length inch	1.73 in
Dimension - Outside Diameter inch	1.06 in

Dimension - Length BB inch	1.73 in
Dimension - Length Overall inch	4.50 in

General

Plated	Y
Color Code	Brown
Trade Name	HYREDUCER™
Die Index	• 20 • 299
UPC	781810308271
Material	Copper
Plating Type	Tin Plated
UPC 14 Digit GTIN	00781810308271

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2775
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)