



YRB3434TW, Copper - Compression Reducer



By Burndy
Catalog # [YRB3434TW](#)

Copper Hyreducer; 4.5 in L; Hot Tin Dipped

Features

- Copper Compression Reducer Splice
- Hot Tin Dipped

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	500 kcmil
Conductor - Copper Str Size B	500 kcmil

Dimensions

Dimension - B Length inch	1.73 in
Dimension - Outside Diameter inch	1.06 in

Dimension - Length BB inch	1.73 in
Dimension - Length Overall inch	4.50 in

General

Color Code	Brown
Trade Name	HYREDUCER™
Die Index	• 20 • 299
UPC	781810192887
Material	Copper
Plating Type	Tin - Hot Dipped
UPC 14 Digit GTIN	00781810192887

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3700
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)