



YRB34U28TW, Aluminum - Compression Reducer

By Burndy
Catalog # [YRB34U28TW](#)

HYREDUCER™, Hot tin dipped, 6.00" long



Features

- Aluminum Compression Reducer Splice
- Hot Tin Dipped

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	500 kcmil
Conductor - Copper Str Size B	4/O AWG
Conductor - AL Str Size A	500 kcmil
Conductor - AL Str Size B	4/O AWG

Configuration

Connector Type	Reducer
----------------	---------

Dimensions

Dimension - B Length fraction	2-7/10 in
Dimension - B Length inch	2.70 in
Dimension - Outside Diameter inch	1.31 in
Dimension - Length Overall inch	6.00 in
Dimension - Strip Length inch	2-13/16 in

General

Color Code	Pink
Trade Name	HYREDUCER™
Die Index	300
UPC	781810209127
Material	Aluminum
Plating Type	Tin - Hot Dipped
UPC 14 Digit GTIN	00781810209127

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2400
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)