



YRB36U36TW, Aluminum HYREDUCER Splice, Tin Plated

By Burndy
Catalog # [YRB36U36TW](#)

HYREDUCER™-600/600, 6.74" long



Features

- Aluminum Compression Reducer Splice
- Hot Tin Dipped

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	600 kcmil
Conductor - Copper Str Size B	600 kcmil
Conductor - AL Str Size A	600 kcmil
Conductor - AL Str Size B	600 kcmil

Configuration

Connector Type	Reducer
----------------	---------

Dimensions

Dimension - B Length inch	2.87 in
Dimension - Length Overall	6.74 in
inch	
Dimension - Strip Length inch	3 in

General

Color Code	Yellow
Trade Name	HYREDUCER™
Die Index	936
UPC	781810454893
Material	Aluminum
Plating Type	Tin - Hot Dipped
UPC 14 Digit GTIN	00781810454893

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2400
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)