



YRB3931TW, Copper - Compression Reducer



By Burndy
Catalog # [YRB3931TW](#)

Copper Hyreducer; 4.75 in L; Hot Tin Dipped

Features

- Copper Compression Reducer Splice
- Hot Tin Dipped

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	750 kcmil
Conductor - Copper Str Size B	350 kcmil

Dimensions

Dimension - B Length inch	2.06 in
Dimension - Outside Diameter inch	1.30 in

Dimension - Length BB inch	2.06 in
Dimension - Length Overall inch	4.75 in

General

Color Code	Black
Trade Name	HYREDUCER™
Die Index	24
UPC	781810192894
Material	Copper
Plating Type	Tin - Hot Dipped
UPC 14 Digit GTIN	00781810192894

Logistics

Minimum Pack Quantity	1
Pallet Quantity	870
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)