



YRB3936TW, Copper - Compression Reducer



By Burndy
Catalog # [YRB3936TW](#)

HYREDUCER

Features

- Copper Compression Reducer Splice
- Hot Tin Dipped

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	750 kcmil
Conductor - Copper Str Size B	600 kcmil

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

Dimension - B Length inch	2.06 in
Dimension - Outside Diameter inch	1.30 in
Dimension - Length BB inch	2.06 in
Dimension - Length Overall inch	4.75 in

General

Color Code	Black
Trade Name	HYREDUCER™
Die Index	24
UPC	781810246924
Material	Copper
Plating Type	Tin - Hot Dipped
UPC 14 Digit GTIN	00781810246924

Logistics

Minimum Pack Quantity	15
Pallet Quantity	2220
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)