



YRB3937TW, Copper HYREDUCER Splice, Tin Plated



By Burndy
Catalog # [YRB3937TW](#)

HYREDUCER-750/650-HOTTIN

Features

- Copper Compression Reducer Splice
- Hot Tin Dipped

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	750 kcmil
Conductor - Copper Str Size B	650 kcmil

Dimensions

Dimension - B Length inch	2.06 in
Dimension - Outside Diameter inch	1.30 in

Dimension - Length BB inch	2.06 in
Dimension - Length Overall inch	4.75 in

General

Color Code	Black
Trade Name	HYREDUCER™
Die Index	24
UPC	781810246900
Material	Copper
Plating Type	Tin - Hot Dipped
UPC 14 Digit GTIN	00781810246900

Logistics

Minimum Pack Quantity	1
Pallet Quantity	4440
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)