



YRB39U31TW, Aluminum - Compression Reducer

By Burndy
Catalog # [YRB39U31TW](#)

Hyreducer Splice



Features

- Aluminum Compression Reducer Splice
- Hot Tin Dipped

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	750 kcmil
Conductor - Copper Str Size B	350 kcmil
Conductor - AL Str Size A	750 kcmil
Conductor - AL Str Size B	350 kcmil

Configuration

Connector Type	Reducer
----------------	---------

Dimensions

Dimension - B Length fraction	2-87/100 in
Dimension - B Length inch	2.87 in
Dimension - Outside Diameter	1.46 in
Dimension - Length Overall	6.74 in
Dimension - Strip Length inch	3

General

Color Code	Yellow
Trade Name	HYREDUCER™
Die Index	936
UPC	781810192757
Material	Aluminum
Plating Type	Tin - Hot Dipped
UPC 14 Digit GTIN	00781810192757

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1200
Carton Quantity	5

Product Assets

[Catalog \[English\]](#)