



YRB4037TTN, Copper HYREDUCER Splice, Tin Plated



By Burndy
Catalog # [YRB4037TTN](#)

HYREDUCER TIN PLATED

Features

- Copper Compression Reducer Splice
- Tin Plated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	800 kcmil
Conductor - Copper Str Size B	650 kcmil

Dimensions

Dimension - B Length inch	2.13 in
Dimension - Outside Diameter inch	1.35 in

Dimension - Length BB inch	2.13 in
Dimension - Length Overall inch	4.89 in

General

Plated	Y
Color Code	Orange
Trade Name	HYREDUCER™
Die Index	25
UPC	781810276587
Material	Copper
Plating Type	Tin Plated
UPC 14 Digit GTIN	00781810276587

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2220
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)