



YRB4444TW, Copper - Compression Reducer



By Burndy
Catalog # [YRB4444TW](#)

Cu Splice, 1000 kcmil(Cu)(Barrel A & B), 35 kV

Features

- Copper Compression Reducer Splice
- Hot Tin Dipped

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	1000 kcmil
Conductor - Copper Str Size B	1000 kcmil

Dimensions

Dimension - B Length inch	2.50 in
---------------------------	---------

Dimension - Outside Diameter	1.50 in
Dimension - Length BB inch	2.50 in
Dimension - Length Overall	5.86 in

General

Trade Name	HYREDUCER™
UPC	781810209165
Material	Copper
Plating Type	Tin - Hot Dipped
UPC 14 Digit GTIN	00781810209165

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1350
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)