



YRB44U39TW, Aluminum - Compression Reducer

By Burndy
Catalog # [YRB44U39TW](#)

Aluminium Hyreducer Splice



Features

- Aluminum Compression Reducer Splice
- Hot Tin Dipped

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	1000 kcmil
Conductor - Copper Str Size B	750 kcmil 700 kcmil
Conductor - AL Str Size A	1000 kcmil
Conductor - AL Str Size B	750 kcmil 700 kcmil

Configuration

Connector Type	Reducer
----------------	---------

Dimensions

Package Height	0.000 in
----------------	----------

Dimension - B Length fraction	2-87/100 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	2.87 in
Dimension - Outside Diameter inch	1.46 in
Dimension - Length Overall inch	6.74 in

General

Color Code	Yellow
Trade Name	HYREDUCER™
Die Index	936
UPC	781810192801
Material	Aluminum
Plating Type	Tin - Hot Dipped
UPC 14 Digit GTIN	00781810192801

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1200
Carton Quantity	5

Product Assets

[Catalog \[English\]](#)