



YRB4C4CTTN, Copper - Compression Reducer



By Burndy
Catalog # [YRB4C4CTTN](#)

Cu Splice, #4 Str(Cu)(Barrel A & B), 35 kV

Features

- Copper Compression Reducer Splice
- Tin Plated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	4 AWG
Conductor - Copper Str Size B	4 AWG

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	52 mm
mm	

Dimension - B Length inch	0.90 in
Dimension - Outside Diameter inch	0.34 in
Dimension - Length BB inch	0.90 in
Dimension - Length Overall inch	2.05 in

General

Plated	Y
Color Code	Gray
Trade Name	HYREDUCER™
Die Index	• 8 • 346
UPC	781810238554
Material	Copper
Plating Type	Tin Plated
UPC 14 Digit GTIN	00781810238554

Logistics

Minimum Pack Quantity	1
Pallet Quantity	48000
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)