


YS1CPULL, Compression Splice, 1 AWG Copper, Long Barrel

By Burndy
Catalog # [YS1CPULL](#)



1 AWG, CU, Long Barrel SPLICE

Features

- Copper Compression Splice, Long Barrel
- Four Center Conductor Stops

Application

Wire Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Size	1 AWG
Conductor - Material	COPPER
Wire Size	4/0 AWG
Conductor Type	CODE
Conductor - Copper Str Size Range	1 AWG
Conductor - Copper Str Size	4/0 AWG

Configuration

Connector Type	LONG BARREL
----------------	-------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	78 mm
Dimension - B Length inch	1.35 in
Dimension - Length Overall inch	3.06 in

General

Feature - Barrel Type	Long
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Green
Trade Name	HYLINK™
Sub Brand	SPLICE, HYLINK
Die Index	11
UPC	781810090084
Type	YS
Material	Copper
Plating Type	Tin - Bright
Finish Type	Tin-Plated
UPC 12 Digit	781810090084
UPC 14 Digit GTIN	00781810090084

Logistics

Minimum Pack Quantity	1
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)