



YS25AT, Aluminum - Compression Splice

By Burndy
Catalog # [YS25AT](#)

High Voltage Uninsulated Al Tube Compression Splice, 1/0 Str Al Cable, 4.73" L

Features

- Aluminum Compression Splice
- Uninsulated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	1/0 AWG
-------------------------	---------

Configuration

Physical Attribute - Number of Crimps Required	2
Connector Type	Splice

Dimensions

Dimension - Pad Width inch	2.29 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

Dimension - L Length Overall mm	120 mm
Dimension - B Length inch	1.96 in
Dimension - Outside Diameter inch	0.60 in
Dimension - Length Overall inch	4.73 in
Dimension - Strip Length inch	2 5/8

General

Feature - Barrel Type	Standard
Feature - Barrel Style	Tapered
Plated	Y
Color Code	Tan
Trade Name	HYLINK™
Die Index	296
UPC	781810001363
Material	Aluminum
Plating Type	Tin - Electro Plated
UPC 14 Digit GTIN	00781810001363

Logistics

Minimum Pack Quantity	1
Pallet Quantity	23200
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)