



YS26AT, Aluminum - Compression Splice

By Burndy
Catalog # [YS26AT](#)

High Voltage Uninsulated Al Tube Compression Splice, 2/0 Str Al Cable, 4.29" L



Features

- Aluminum Compression Splice
- High Voltage Uninsulated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	2/0 AWG
-------------------------	---------

Configuration

Physical Attribute - Number of	3
Crimps Required	
Connector Type	Splice

Dimensions

Dimension - Pad Width inch	2.04 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

Dimension - L Length Overall	109 mm
Dimension - B Length inch	1.83 in
Dimension - Outside Diameter	0.67 in
inch	
Dimension - Length Overall	4.29 in
inch	
Dimension - Strip Length inch	2 3/8

General

Feature - Barrel Type	Standard
Feature - Barrel Style	Tapered
Plated	Y
Color Code	Olive
Trade Name	HYLINK™
Die Index	297
UPC	781810001370
Insulation	Y
Material	Aluminum
Plating Type	Tin - Electro Plated
UPC 14 Digit GTIN	00781810001370

Logistics

Minimum Pack Quantity	1
Pallet Quantity	14800
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)