



YS26FXLTCKITC, Compression Splice Kit with Clear Heat Shrink, 2/0 Flex G,H,I,K,M, DLO, 2/0 AWG Cu

By Burndy
Catalog # YS26FXLTCKITC

2/0 Flex G,H,I,K,M,DLO, 2/0 AWG, CU, SPLICE KIT with Clear Heat Shrink

Features

- In-line splice kit includes compression splice connector and heat shrink
- Barrel is designed with internal chamfer at the wire entry to ensure smooth insertion of wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Splice

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Wire Size	1/0 WG
Conductor - Copper Flex K Size Range	2/0 AWG
Conductor - Copper Flex K Size A	2/0 AWG
Conductor - Copper Flex K Size B	2/0 AWG
Conductor - Copper Flex M Size B	2/0 AWG
Conductor - Copper Flex M Size A	2/0 AWG
Conductor - Copper Flex M Size	2/0 AWG
Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Flex I Size B	2/0 AWG
Conductor - Copper Flex I Size Range	2/0 AWG
Conductor - Copper Flex G Size A	2/0 AWG
Conductor - Copper Flex G Size	2/0 AWG



Conductor - Copper Flex G Size B	2/0 AWG
Conductor - Copper DLO Size Range	2/0 AWG
Conductor - Copper DLO Size	2/0 AWG
Conductor Size	2/0 AWG
Conductor - Copper Flex H Size A	2/0 AWG
Conductor - Copper Flex H Size	2/0 AWG
Conductor - Copper Flex G Size Range	2/0 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Flex H Size B	2/0 AWG
Conductor - Copper Str Size Range	2/0 AWG
Conductor - Copper Flex H Size Range	2/0 AWG
Conductor - Copper Flex I Size A	2/0 AWG
Conductor - Copper Flex I Size	2/0 AWG

Configuration

Connector Type	STANDARD BARREL KITS
----------------	----------------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	66.5 mm
Dimension - Strip Length inch	1.10
Dimension - B Length inch	1.10 in
Dimension - Length BB inch	1.10 in
Dimension - Length Overall inch	2.62 in

General

Trade Name	HYLINK™
------------	---------

Die Index	13
Die Index Run Side	13
Die Index Tap Side	13
Feature - Barrel Type	Standard
Feature - Barrel Style	Skived
Plated	Y
Color Code	Black
UPC	781810344125
Color Code - Side B	Black
Color Code - Side A	Black
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated

UPC 12 Digit	781810344125
UPC 14 Digit GTIN	00781810344125

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1080
Carton Quantity	12

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)



A Hubbell brand