



YS26LTCKITC, Compression Splice Kit with Clear Heat Shrink, 2/0 AWG Cu

By Burndy
Catalog # [YS26LTCKITC](#)

2/0 AWG, CU, SPLICE KIT with Clear Heat Shrink



Features

- In-line splice kit includes compression splice connector and heat shrink
- Barrel is designed with internal chamfer at the wire entry to ensure smooth insertion of wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Size	2/0 AWG
Conductor - Copper Str Size B	2/0
Conductor - Material	COPPER
Wire Size	1000 KCMIL
Conductor Type	CODE
Conductor - Copper Str Size Range	2/0 AWG
Conductor - Copper Str Size	1000 KCMIL

Configuration

Connector Type	STANDARD BARREL KITS
----------------	----------------------

Current

Voltage Rating	35 kV
----------------	-------

Voltage - Maximum	35000
-------------------	-------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	61.2 mm
Dimension - B Length inch	1.16 in
Dimension - Length BB inch	1.16 in
Dimension - Length Overall	2.41 in
inch	

General

Feature - Barrel Type	Standard
Feature - Barrel Style	Skived
Plated	Y
Color Code	Black
Trade Name	HYLINK™
Die Index	13
Die Index Run Side	13
UPC	781810346334
Color Code - Side B	Black
Die Index Tap Side	13
Color Code - Side A	Black
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810346334
UPC 14 Digit GTIN	00781810346334

Logistics

Minimum Pack Quantity	12
Pallet Quantity	90
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)