

YS27AT, Aluminum - Compression Splice

By Burndy
Catalog # [YS27AT](#)

High Voltage Uninsulated Al Tube Compression Splice, 3/0 Str Al Cable, 4.69" L



Features

- Aluminum Compression Splice
- High Voltage Uninsulated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	3/0 AWG
-------------------------	---------

Configuration

Physical Attribute - Number of	3
Crimps Required	
Connector Type	Splice

Dimensions

Dimension - Pad Width inch	2.27 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

Dimension - L Length Overall	119 mm
Dimension - B Length inch	2.04 in
Dimension - Outside Diameter	0.76 in
inch	
Dimension - Length Overall	4.69 in
inch	
Dimension - Strip Length inch	2 5/8

General

Feature - Barrel Type	Standard
Feature - Barrel Style	Tapered
Plated	Y
Color Code	Ruby
Trade Name	HYLINK™
Die Index	467
UPC	781810001387
Material	Aluminum
Plating Type	Tin - Electro Plated
UPC 14 Digit GTIN	00781810001387

Logistics

Minimum Pack Quantity	1
Pallet Quantity	14800
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)