



YS28AT, Aluminum - Compression Splice

By Burndy
Catalog # [YS28AT](#)

Aluminum Compression Splice, 4/0 AWG, 5.05" Splice Length,
Long Barrel, Tapered End, Tin Plated



Features

- Aluminum Compression Splice
- Tapered End
- Tin Plated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	4/0 AWG
-------------------------	---------

Configuration

Physical Attribute - Number of	3
Crimps Required	
Connector Type	Splice

Dimensions

Dimension - Pad Width inch	2.42 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

Dimension - L Length Overall	128 mm
Dimension - B Length inch	2.16 in
Dimension - Outside Diameter	0.85 in
Dimension - Length Overall	5.05 in
Dimension - Strip Length inch	2 3/4

General

Feature - Barrel Type	Standard
Feature - Barrel Style	Tapered
Plated	Y
Color Code	White
Trade Name	HYLINK™
Die Index	298
UPC	781810001394
Material	Aluminum
Plating Type	Tin - Electro Plated
UPC 14 Digit GTIN	00781810001394

Logistics

Minimum Pack Quantity	1
Pallet Quantity	12000
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)