



YS2CAT, Aluminum - Compression Splice

By Burndy
Catalog # [YS2CAT](#)

Al Comp Splice,High Voltage Uninsul, Tapered Ends, #2 Str(Al),
35 KV, 4.00" L, 348 Index

Features

- Aluminum Compression Splice
- High Voltage Uninsulated
- Tapered Ends

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	2 AWG
-------------------------	-------

Configuration

Physical Attribute - Number of	2
Crimps Required	
Connector Type	Splice

Dimensions

Dimension - Pad Width inch	1.93 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

Dimension - L Length Overall	102 mm
Dimension - B Length inch	1.58 in
Dimension - Outside Diameter	0.53 in
Dimension - Length Overall	4.00 in
Dimension - Strip Length inch	2 1/4

General

Feature - Barrel Type	Standard
Feature - Barrel Style	Tapered
Plated	Y
Color Code	Pink
Trade Name	HYLINK™
Die Index	348
UPC	781810001356
Material	Aluminum
Plating Type	Tin - Electro Plated
UPC 14 Digit GTIN	00781810001356

Logistics

Minimum Pack Quantity	1
Pallet Quantity	19600
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)