


YS2CPULL, Compression Splice, 2 AWG Cu, Long Barrel

By Burndy
Catalog # [YS2CPULL](#)



2 AWG, CU, Long Barrel SPLICE

Features

- Copper Compression Splice, Long Barrel
- Four center conductor stops

Application

Wire Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Size	2 AWG
Conductor - Material	COPPER
Conductor Type	CODE
Conductor - Copper Str Size Range	2 AWG
Conductor - Copper Str Size	2 AWG

Configuration

Connector Type	LONG BARREL
----------------	-------------

Current

Voltage Rating	35 kV
----------------	-------

Voltage - Maximum	35000
-------------------	-------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	72 mm
Dimension - B Length inch	1.22 in
Dimension - Length Overall inch	2.82 in

General

Feature - Barrel Type	Long
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Brown
Trade Name	HYLINK™
Sub Brand	SPLICE, HYLINK
Die Index	10
UPC	781810090190
Type	Type YS
Material	Copper
Plating Type	Tin - Bright
Finish Type	Tin-Plated
UPC 12 Digit	781810090190
UPC 14 Digit GTIN	00781810090190

Logistics

Minimum Pack Quantity	1
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)