



YS2UCG1, Splice Kit - Insulated

By Burndy
Catalog # YS2UCG1

URD Insulator Splice Kit, #1 - #2 Str Al, #2 AWG (6-1, 7-1) ACSR,
#1 - #2 Str Cu, 600 V

Features

- URD Insulator Splice Kit

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	2 AWG 1 AWG
Conductor - Copper Str Size B	2 AWG 1 AWG
Conductor - Copper Str Size A Range	2 AWG-1 AWG
Conductor - AL Str Size A	2 AWG 1 AWG
Conductor - AL Str Size B	2 AWG 1 AWG
Conductor - AL Str Size A Range	2 AWG-1 AWG
Conductor - AL Str Size B Range	2 AWG-1 AWG
Conductor - ACSR Str Size A	2 (6/1) Sparrow AWG 2 (7/1) Sparate AWG
Conductor - ACSR Str Size B	2 (6/1) Sparrow AWG 2 (7/1) Sparate AWG
Conductor - ACSR Str Size A Range	2 (6/1) Sparrow AWG-2 (7/1) Sparate AWG
Conductor - Copper Str Size B Range	2 AWG-1 AWG



Conductor - ACSR Str Size B Range	2 (6/1) Sparrow AWG-2 (7/1) Sparate AWG
-----------------------------------	---

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	0.87 in
Dimension - Length Overall inch	2 in

General

Plated	N
Insulation Type	Diaform
Die Index	243 - BG
UPC	781810187708
Insulation	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810187708
UPC 14 Digit GTIN	00781810187708

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1440
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)