



YS30A1, Compression Splice, 300 kcmil AL9CU

By Burndy
Catalog # [YS30A1](#)

300 KCMIL, AL, SPLICE, AL9CU



Features

- Aluminum splices are dual rated to accommodate both copper and aluminum wire
- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Clearly marked with wire size, die index, color code, and crimp location bands
- Factory pre-filled with PENETROX™ Type A13 oxide inhibitor
- Color coded end caps inserted in the barrels to match the die color code and prevent foreign materials from entering the barrel

Application

Wire Splice

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	ALUMINUM / COPPER
Wire Size	300 KCMIL
Conductor - AL Str Size	300 KCMIL
Conductor - AL Str Size Range	300 kcmil
Conductor - Copper Str Size	300 KCMIL
Conductor - Copper Str Range	300
Conductor Size	300 KCMIL
Conductor Type	CODE
Conductor - Copper Str Size Range	300 kcmil

Configuration

Connector Type	DUAL RATED
----------------	------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Outside Diameter	1.01 in
Package Width	0.000 in
Dimension - L Length Overall mm	81 mm
Dimension - Outside Diameter inch	1.01 in
Dimension - Strip Length inch	1-3/4 in
Length	3.2 in
Dimension - B Length fraction	1-1/2 in
Dimension - B Length inch	1.47 in
Dimension - Length Overall inch	3.20 in

General

Trade Name	HYLINK™
Die Index	470
Feature - Barrel Type	Long
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Blue
Sub Brand	HYLINK
UPC	781810757406
Type	YS-A, Standard Barrel
Material	Aluminum
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810757406
UPC 14 Digit GTIN	00781810757406

Logistics

Minimum Pack Quantity	1
Carton Quantity	2

Operational



A Hubbell brand