

YS30AT, Aluminum - Compression Splice

By Burndy
Catalog # [YS30AT](#)

Al Compression Splice, 300 Kcmil, 5.91 IN L, Tin Plated, 470 Index



Features

- Aluminum Compression Splice
- Tin Plated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	300 kcmil
-------------------------	-----------

Configuration

Physical Attribute - Number of	3
Crimps Required	
Connector Type	Splice

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	150 mm

Dimension - B Length inch	2.54 in
Dimension - Outside Diameter inch	1.01 in
Dimension - Inside Diameter inch	0.65 in
Dimension - Length Overall inch	5.91 in
Dimension - Strip Length inch	3 1/8

General

Feature - Barrel Type	Standard
Feature - Barrel Style	Tapered
Plated	Y
Color Code	Blue
Trade Name	HYLINK™
Die Index	470
UPC	781810094372
Insulation	Y
Material	Aluminum
Plating Type	Tin - Electro Plated
UPC 14 Digit GTIN	00781810094372

Logistics

Minimum Pack Quantity	1
Pallet Quantity	7400
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)