



Compression Splice

By Burndy
Catalog # [YS30FX](#)

250 KCMIL G&H, 250 AWG CU, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, YELLOW Color Code, 16 Die Index.



Features

- Copper Compression Splice
- Long Barrel with Internal Chamfer

Application

Wire Splice

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	NO
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - CSA Approved	CSA

Conductor

Conductor - Copper Flex G Size	250 KCMIL
Conductor Size	250 KCMIL
Conductor - Copper Flex H Size	250 KCMIL
Conductor - Copper Flex G Size	250 KCMIL
Range	
Conductor - Material	COPPER
Wire Size	250 KCMIL
Conductor Type	FLEX
Conductor - Copper Str Size	250 KCMIL
Conductor - Copper Flex H Size	250 KCMIL
Range	

Configuration

Connector TypeLONG BARREL

Current

Voltage Rating35 kV

Dimensions

Package Height	0.000 in
Length	4.33 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.95

General

Color Code	Yellow
Trade Name	HYLINK™
Sub Brand	HYLINK
Die Index	16
UPC	621945624122
Type	YS
Construction Material - Main	Copper
Material	COPPER
Finish Type	Tin-Plated

Logistics

Carton Quantity10

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[French, English\]](#)