



Compression Splice

By Burndy
Catalog # [YS30LFX](#)

250 KCMIL G,H, 250 AWG CU, Standard Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, YELLOW Color Code, 16 Die Index.

Features

- Copper Compression Splice
- Standard Barrel with Internal Chamfer

Application

Wire Splice

Specifications

Buy American Compliant Certification - cULus	Contact Manufacturer NO
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - CSA Approved	CSA

Conductor

Conductor - Copper Flex G Size	250 KCMIL
Conductor Size	250 KCMIL
Conductor - Copper Flex H Size	250 KCMIL
Conductor - Copper Flex G Size Range	250 KCMIL
Conductor - Material	COPPER
Wire Size	250 KCMIL
Conductor Type	FLEX
Conductor - Copper Str Size	250 KCMIL
Conductor - Copper Flex H Size Range	250 KCMIL

Configuration

Connector Type	STANDARD BARREL
----------------	-----------------

Current

Voltage Rating	35 kV
----------------	-------

Dimensions

Length	2.46 in
Dimension - B Length inch	1.01

General

Color Code	Yellow
Trade Name	HYLINK™
Sub Brand	HYLINK
Die Index	16
UPC	621945623989
Type	YS
Construction Material - Main Material	Copper
Finish Type	COPPER
	Tin-Plated

Logistics

Carton Quantity	6
-----------------	---

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[French, English\]](#)