

Compression Splice

By Burndy
Catalog # [YS31FX](#)

Copper Compression Splice



Features

- Copper Compression Splice
- Long Barrel with Internal Chamfer

Application

Wire Splice

Specifications

Buy American Compliant Certification - cULus	Contact Manufacturer NO
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified Industry Standard(s)	Contact Manufacturer UL 486A-486B
Certification - CSA Approved	CSA

Conductor

Conductor - Copper DLO Size Range	262 KCMIL
Conductor Size	250 KCMIL
Conductor - Material	COPPER
Wire Size	250 KCMIL
Conductor - Copper Flex K Size Range	250 KCMIL
Conductor - Copper Flex K Size	250 KCMIL
Conductor - Copper Flex M Size	250 KCMIL
Conductor Type	FLEX
Conductor - Copper Str Size	250 KCMIL
Conductor - Copper Flex I Size	250 KCMIL
Conductor - Copper Flex I Size Range	250 KCMIL

Configuration

Connector Type	LONG BARREL
----------------	-------------

Current

Voltage Rating	35 kV
----------------	-------

Dimensions

Length	4.35 in
Dimension - B Length inch	1.95

General

Color Code	White
Trade Name	HYLINK™
Sub Brand	HYLINK
Die Index	17
UPC	621945624139
Type	YS
Construction Material - Main Material	Copper COPPER
Finish Type	Tin-Plated

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
[Installation Manual \[French, English\]](#)