



Compression Splice

By Burndy
Catalog # [YS31LFX](#)

Copper Compression Splice

Features

- Copper Compression Splice
- Standard Barrel with Internal Chamfer

Application

Wire Splice

Specifications

Buy American Compliant Certification - cULus	Contact Manufacturer NO
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - CSA Approved	CSA

Conductor

Conductor - Copper DLO Size Range	262 KCMIL
Conductor - Copper DLO Size	262 KCMIL
Conductor Size	250 KCMIL
Conductor - Material	COPPER
Wire Size	250 KCMIL
Conductor - Copper Flex K Size Range	250 KCMIL
Conductor - Copper Flex K Size	250 KCMIL
Conductor - Copper Flex M Size	250 KCMIL
Conductor Type	FLEX
Conductor - Copper Str Size	250 KCMIL
Conductor - Copper Flex I Size	250 KCMIL

Conductor - Copper Flex I Size 250 KCMIL Range

Configuration

Connector Type STANDARD BARREL

Current

Voltage Rating 35 kV

Dimensions

Length 2.6 in
Dimension - B Length inch 1.07

General

Color Code	White
Trade Name	HYLINK™
Sub Brand	HYLINK
Die Index	17
UPC	621945623866
Type	YS
Construction Material - Main Material	Copper COPPER
Finish Type	Tin-Plated

Logistics

Carton Quantity 60

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[French, English\]](#)