

Compression Splice

By Burndy
Catalog # [YS32FX](#)

Copper Compression Splice



Features

- Copper Compression Splice
- Long Barrel with Internal Chamfer

Application

Wire Splice

Specifications

Buy American Compliant Certification - cULus	Contact Manufacturer NO
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - CSA Approved	CSA

Conductor

Conductor - Copper Flex G Size	300 KCMIL
Conductor - Copper DLO Size	313 KCMIL
Range	
Conductor - Copper DLO Size	313 KCMIL
Conductor Size	300 KCMIL
Conductor - Copper Flex H Size	300 KCMIL
Conductor - Copper Flex G Size	300 KCMIL
Range	
Conductor - Material	COPPER
Wire Size	300 KCMIL
Conductor - Copper Flex K Size	300 KCMIL
Range	
Conductor - Copper Flex K Size	300 KCMIL
Conductor - Copper Flex M Size	300 KCMIL
Conductor Type	FLEX
Conductor - Copper Str Size	300 KCMIL
Conductor - Copper Flex H Size	300 KCMIL
Range	
Conductor - Copper Flex I Size	300 kcmil

Conductor - Copper Flex I Size 300 KCMIL
Range

Configuration

Connector Type LONG BARREL

Current

Voltage Rating 35 kV

Dimensions

Package Height	0.000 in
Length	4.61 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	2.07

General

Color Code	Red
Trade Name	HYLINK™
Sub Brand	HYLINK
Die Index	18
UPC	621945624146
Type	YS
Construction Material - Main	Copper
Material	COPPER
Finish Type	Tin-Plated

Logistics

Carton Quantity 6

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[French, English\]](#)