



Compression Splice

By Burndy
Catalog # [YS32LFX](#)

300 KCMIL G,H,I,K,M, 313 DLO, 300 AWG CU, Standard Barrel,
Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, RED
Color Code, 18 Die Index.

Features

- Copper Compression Splice
- Standard Barrel with Internal Chamfer

Application

Wire Splice

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	NO
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - CSA Approved	CSA

Conductor

Conductor - Copper Flex G Size	300 KCMIL
Conductor - Copper DLO Size	313 KCMIL
Range	
Conductor - Copper DLO Size	313 KCMIL
Conductor Size	300 KCMIL
Conductor - Copper Flex H Size	300 KCMIL
Conductor - Copper Flex G Size	300 KCMIL
Range	
Conductor - Material	COPPER
Wire Size	300 KCMIL
Conductor - Copper Flex K Size	300 KCMIL
Range	
Conductor - Copper Flex K Size	300 KCMIL
Conductor - Copper Flex M Size	300 KCMIL
Conductor Type	FLEX
Conductor - Copper Str Size	300 KCMIL

Conductor - Copper Flex H Size	300 KCMIL
Range	
Conductor - Copper Flex I Size	300 kcmil
Conductor - Copper Flex I Size	300 KCMIL
Range	

Configuration

Connector Type	STANDARD BARREL
----------------	-----------------

Current

Voltage Rating	35 kV
----------------	-------

Dimensions

Length	2.74 in
Dimension - B Length inch	1.14

General

Color Code	Red
Trade Name	HYLINK™
Sub Brand	HYLINK
Die Index	18
UPC	621945623996
Type	YS
Construction Material - Main	Copper
Material	COPPER
Finish Type	Tin-Plated

Logistics

Carton Quantity	6
-----------------	---

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[French, English\]](#)