



YS34AT, Aluminum - Compression Splice

By Burndy
Catalog # [YS34AT](#)

High Voltage Uninsulated Al Tube Compression Splice, 500 kcmil
Al Cable, 7.79" L



Features

- Aluminum Compression Splice
- High Voltage Uninsulated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	500 kcmil
-------------------------	-----------

Configuration

Physical Attribute - Number of	6
Crimps Required	
Connector Type	Splice

Dimensions

Dimension - Pad Width inch	3.79 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

Dimension - L Length Overall	198 mm
Dimension - B Length inch	3.39 in
Dimension - Outside Diameter	1.32 in
inch	
Dimension - Length Overall	7.79 in
inch	
Dimension - Strip Length inch	4 1/8

General

Feature - Barrel Type	Standard
Feature - Barrel Style	Tapered
Plated	Y
Color Code	Pink
Trade Name	HYLINK™
Die Index	300
UPC	781810757611
Material	Aluminum
Plating Type	Tin - Electro Plated
UPC 14 Digit GTIN	00781810757611

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3600
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)