



Compression Splice

By Burndy
Catalog # [YS34FX](#)

350 KCMIL G,H,I,K,M, 373 DLO, 350 AWG CU, Long Barrel,
Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, BLUE
Color Code, 19 Die Index.

Features

- Copper Compression Splice
- Long Barrel with Internal Chamfer

Application

Wire Splice

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	NO
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - CSA Approved	CSA

Conductor

Conductor - Copper Flex G Size	350 KCMIL
Conductor - Copper DLO Size	373 KCMIL
Range	
Conductor - Copper DLO Size	373 KCMIL
Conductor Size	350 KCMIL
Conductor - Copper Flex H Size	350 KCMIL
Conductor - Copper Flex G Size	350 KCMIL
Range	
Conductor - Material	COPPER
Wire Size	350 KCMIL
Conductor - Copper Flex K Size	350 KCMIL
Range	
Conductor - Copper Flex K Size	350 KCMIL
Conductor - Copper Flex M Size	350 KCMIL
Conductor Type	FLEX
Conductor - Copper Str Size	350 KCMIL

Conductor - Copper Flex H Size 350 KCMIL
Range

Conductor - Copper Flex I Size 350 KCMIL

Conductor - Copper Flex I Size 350 KCMIL
Range

Configuration

Connector Type LONG BARREL

Current

Voltage Rating 35 kV

Dimensions

Length 4.91 in
Dimension - B Length inch 2.2

General

Color Code	Blue
Trade Name	HYLINK™
Sub Brand	HYLINK
Die Index	19
UPC	621945624153
Type	YS
Construction Material - Main	Copper
Material	COPPER
Finish Type	Tin-Plated

Logistics

Carton Quantity 6

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[French, English\]](#)