



YS34FXLTCKITC, Compression Splice Kit with Clear Heat Shrink, 350 kcmil G,H,I,K,M, 373 DLO, Cu

By Burndy
Catalog # YS34FXLTCKITC

350 kcmil G,H,I,K,M,373 DLO, CU, SPLICE KIT with Clear Heat Shrink

Features

- In-line splice kit includes compression splice connector and heat shrink
- Barrel is designed with internal chamfer at the wire entry to ensure smooth insertion of wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Splice

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Wire Size	350 kcmil G,H,I,K,M,373 DLO
Conductor - Copper Flex K Size Range	350 kcmil
Conductor - Copper Flex K Size A	350 kcmil
Conductor - Copper Flex K Size B	350 kcmil
Conductor - Copper Flex M Size B	350 kcmil
Conductor - Copper Flex M Size A	350 kcmil
Conductor - Copper Str Size	350 Kcmil
Conductor - Copper Flex I Size B	350 kcmil
Conductor - Copper Flex I Size Range	350 kcmil
Conductor - Copper Flex G Size A	350 kcmil



Conductor - Copper Flex G Size B	350 kcmil
Conductor - Copper DLO Size Range	373 kcmil
Conductor Size	350 KCMIL
Conductor - Copper Flex H Size A	350 kcmil
Conductor - Copper Flex G Size Range	350 kcmil
Conductor Type	FLEX
Conductor - Copper Str Size Range	350 kcmil
Conductor - Copper Flex H Size B	350 kcmil
Conductor - Copper Flex H Size Range	350 kcmil
Conductor - Copper Flex I Size A	350 kcmil

Configuration

Connector Type	STANDARD BARREL KITS
----------------	----------------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	98.3 mm
Dimension - Strip Length inch	1.60
Dimension - B Length inch	1.60 in
Dimension - Length BB inch	1.60 in
Dimension - Length Overall inch	3.87 in

General

Trade Name	HYLINK™
Die Index	19
Die Index Run Side	• 19 • L80

Die Index Tap Side	• 19 • L80
Feature - Barrel Type	Standard
Feature - Barrel Style	Skived
Plated	Y
Color Code	Blue
UPC	781810344040
Color Code - Side B	Blue
Color Code - Side A	Blue
Type	YS-TC
Construction Material - Main	Copper
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated

UPC 12 Digit	781810344040
UPC 14 Digit GTIN	00781810344040

Logistics

Minimum Pack Quantity	12
Pallet Quantity	90
Carton Quantity	1

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)



A Hubbell brand