YS34L, Cu Compression Splice, Standard Barrel, 500 kcmil

By Burndy
Catalog # YS34L

500 kcmil, CU, Standard Barrel SPLICE

Features

- Copper seamless barrel with center stop indentations to indicate when wire is fully inserted into each side of the barrel
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Splice

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	500 kcmil
Conductor - Copper Str Size	500 kcmil
Conductor - Copper Str Compact Size	500
Conductor Size	500 KCMIL
Conductor Type	CODE
Conductor - Copper Str Size Range	500 kcmil

Configuration

Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	80 mm
Dimension - Strip Length inch	1-7/16
Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.38 in
Dimension - Length Overall inch	3.15 in

General

Trade Name	HYLINK™
Die Index	20
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Brown
Sub Brand	HYLINK
UPC	781810508558
Type	YS-L, Standard Barrel
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810508558
UPC 14 Digit GTIN	00781810508558

Logistics

Minimum Pack Quantity	1
Carton Quantity	6

Product Assets

Catalog [English]

© 2026 Hubbell Incorporated. All rights reserved