



Compression Splice

By Burndy
Catalog # YS34LFX

350 KCMIL G,H,I,K,M, 373 DLO, 350 AWG CU, Standard Barrel,
Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, BLUE
Color Code, 19 Die Index.

Features

- Copper Compression Splice
- Standard Barrel with Internal Chamfer

Application

Wire Splice

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	NO
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - CSA Approved	CSA

Conductor

Conductor - Copper Flex G Size	350 KCMIL
Conductor - Copper DLO Size	373 KCMIL
Range	
Conductor - Copper DLO Size	373 KCMIL
Conductor Size	350 KCMIL
Conductor - Copper Flex H Size	350 KCMIL
Conductor - Copper Flex G Size	350 KCMIL
Range	
Conductor - Material	COPPER
Wire Size	350 KCMIL
Conductor - Copper Flex K Size	350 KCMIL
Range	
Conductor - Copper Flex K Size	350 KCMIL
Conductor - Copper Flex M Size	350 KCMIL
Conductor Type	FLEX
Conductor - Copper Str Size	350 KCMIL

Conductor - Copper Flex H Size	350 KCMIL
Range	
Conductor - Copper Flex I Size	350 KCMIL
Conductor - Copper Flex I Size	350 KCMIL
Range	

Configuration

Connector Type	STANDARD BARREL
----------------	-----------------

Current

Voltage Rating	35 kV
----------------	-------

Dimensions

Length	3.15 in
Dimension - B Length inch	1.32

General

Color Code	Blue
Trade Name	HYLINK™
Sub Brand	HYLINK
Die Index	19
UPC	621945624009
Type	YS
Construction Material - Main	Copper
Material	COPPER
Finish Type	Tin-Plated

Logistics

Carton Quantity	6
-----------------	---

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[French, English\]](#)