



Compression Splice

By Burndy
Catalog # [YS36FX](#)

500 KCMIL G&H, 444 DLO, 500 AWG CU, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, BROWN Color Code, 20 Die Index.



Features

- Copper Compression Splice
- Long Barrel with Internal Chamfer

Application

Wire Splice

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	NO
EU RoHS Indicator	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - CSA Approved	CSA

Conductor

Conductor - Copper Flex G Size	500 KCMIL
Conductor - Copper DLO Size	444 KCMIL
Range	
Conductor - Copper DLO Size	444 KCMIL
Conductor Size	500 KCMIL
Conductor - Copper Flex H Size	500 KCMIL
Conductor - Copper Flex G Size	500 KCMIL
Range	
Conductor - Material	COPPER
Wire Size	500 KCMIL
Conductor Type	FLEX
Conductor - Copper Str Size	500 KCMIL
Conductor - Copper Flex H Size	500 KCMIL
Range	

Configuration

Connector Type	LONG BARREL
----------------	-------------

Current

Voltage Rating	35 kV
----------------	-------

Dimensions

Length	5.84 in
Dimension - B Length inch	2.62

General

Color Code	Brown
Trade Name	HYLINK™
Sub Brand	HYLINK
Die Index	20
UPC	621945624160
Type	YS
Construction Material - Main	Copper
Material	COPPER
Finish Type	Tin-Plated

Logistics

Carton Quantity	6
-----------------	---

Product Assets

[Catalog \[English\]](#)