



Compression Splice

By Burndy
Catalog # [YS36LFX](#)

500 KCMIL G&H, 444 DLO, 500 AWG CU, Standard Barrel,
Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, BROWN
Color Code, 20 Die Index.

Features

- Copper Compression Splice
- Standard Barrel with Internal Chamfer

Application

Wire Splice

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	NO
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - CSA Approved	CSA

Conductor

Conductor - Copper Flex G Size	500 KCMIL
Conductor - Copper DLO Size	444 KCMIL
Range	
Conductor - Copper DLO Size	444 KCMIL
Conductor Size	500 KCMIL
Conductor - Copper Flex H Size	500 KCMIL
Conductor - Copper Flex G Size	500 KCMIL
Range	
Conductor - Material	COPPER
Wire Size	500 KCMIL
Conductor Type	FLEX
Conductor - Copper Str Size	500 KCMIL

Conductor - Copper Flex H Size 500 KCMIL
Range

Configuration

Connector Type	STANDARD BARREL
----------------	-----------------

Current

Voltage Rating	35 kV
----------------	-------

Dimensions

Length	3.21 in
Dimension - B Length inch	1.31

General

Color Code	Brown
Trade Name	HYLINK™
Sub Brand	HYLINK
Die Index	20
UPC	621945623873
Type	YS
Construction Material - Main	Copper
Material	COPPER
Finish Type	Tin-Plated

Logistics

Carton Quantity	6
-----------------	---

Product Assets

[Catalog \[English\]](#)