


YS36PULL, Compression Splice, 600 kcmil Cu, Long Barrel

By Burndy
Catalog # [YS36PULL](#)



600 kcmil, CU, Long Barrel SPLICE

Features

- Copper Compression Splice, Long Barrel
- Four Center Conductor Stops

Application

Wire Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Size	600 KCMIL
Conductor - Material	COPPER
Conductor Type	CODE
Conductor - Copper Str Size Range	650 kcmil
Conductor - Copper Str Size	600 kcmil

Configuration

Connector Type	LONG BARREL
----------------	-------------

Current

Voltage Rating	35 kV
----------------	-------

Voltage - Maximum	35000
-------------------	-------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	149 mm
Dimension - B Length inch	2.63 in
Dimension - Length Overall inch	5.86 in

General

Feature - Barrel Type	Long
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Green
Trade Name	HYLINK™
Sub Brand	SPLICE, HYLINK
Die Index	22
UPC	781810093436
Type	YS
Material	Copper
Plating Type	Tin - Bright
Finish Type	Tin-Plated
UPC 12 Digit	781810093436
UPC 14 Digit GTIN	00781810093436

Logistics

Minimum Pack Quantity	1
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)