



Compression Splice

By Burndy
Catalog # YS38FX

Copper Compression Splice



Features

- Copper Compression Splice
- Long Barrel with Internal Chamfer

Application

Wire Splice

Specifications

Buy American Compliant Certification - cULus	Contact Manufacturer NO
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - CSA Approved	CSA

Conductor

Conductor - Copper Flex G Size	550 KCMIL
Conductor - Copper DLO Size	535 KCMIL
Range	
Conductor - Copper DLO Size	535 KCMIL
Conductor Size	500-550 KCMIL
Conductor - Copper Flex H Size	500-550 KCMIL
Conductor - Copper Flex G Size	550 KCMIL
Range	
Conductor - Material	COPPER
Wire Size	500-550 KCMIL
Conductor - Copper Flex K Size	500 KCMIL
Range	
Conductor - Copper Flex K Size	500 KCMIL
Conductor Type	FLEX
Conductor - Copper Str Size	500-550 KCMIL
Conductor - Copper Flex H Size	500 - 550 KCMIL
Range	
Conductor - Copper Flex I Size	500-550 KCMIL

Conductor - Copper Flex I Size 500 - 550 KCMIL Range

Configuration

Connector Type LONG BARREL

Current

Voltage Rating 35 kV

Dimensions

Package Height	0.000 in
Length	6.09 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	2.75

General

Color Code	Pink
Trade Name	HYLINK™
Sub Brand	HYLINK
Die Index	L99
UPC	621945624177
Type	YS
Construction Material - Main	Copper
Material	COPPER
Finish Type	Tin-Plated

Logistics

Carton Quantity 6

Product Assets

[Catalog \[English\]](#)