



# YS38FXLTCKITC, Compression Splice Kit with Clear Heat Shrink, 500 kcmil H,I,K, 550 kcmil G,H,I, 535 DLO Cu

By Burndy  
Catalog # [YS38FXLTCKITC](#)

500 kcmil H,I,K / 550 kcmil G,H,I,535 DLO, CU, SPLICE KIT with Clear Heat Shrink

## Features

- In-line splice kit includes compression splice connector and heat shrink
- Barrel is designed with internal chamfer at the wire entry to ensure smooth insertion of wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

## Application

Wire Splice

## Specifications

|                               |    |
|-------------------------------|----|
| Certification - UL Recognized | No |
| Certification - cULus         | No |
| Certification - ETL           | No |
| Standards - RoHS Compliance   | CM |
| Status                        |    |
| UL Listed                     | No |
| Certification - CSA Approved  | No |

## Conductor

|                                      |                                           |
|--------------------------------------|-------------------------------------------|
| Conductor - Material                 | COPPER                                    |
| Wire Size                            | 500 kcmil H,I,K / 550 kcmil G,H,I,535 DLO |
| Conductor - Copper Flex K Size Range | 500 kcmil                                 |
| Conductor - Copper Flex K Size A     | 500 kcmil                                 |
| Conductor - Copper Flex K Size B     | 500 kcmil                                 |
| Conductor - Copper Flex M Size B     | 500 kcmil                                 |
| Conductor - Copper Flex M Size A     | 500 kcmil                                 |
| Conductor - Copper Str Size          | 500 Kcmil                                 |
| Conductor - Copper Flex I Size B     | 500 kcmil                                 |
| Conductor - Copper Flex I Size Range | 500 / 550 kcmil                           |
| Conductor - Copper Flex G Size A     | 500 kcmil                                 |
| Conductor - Copper Flex G Size B     | 500 kcmil                                 |



|                                      |                 |
|--------------------------------------|-----------------|
| Conductor - Copper DLO Size Range    | 535 kcmil       |
| Conductor Size                       | 500-550 KCMIL   |
| Conductor - Copper Flex H Size A     | 500 kcmil       |
| Conductor - Copper Flex G Size Range | 550 kcmil       |
| Conductor Type                       | FLEX            |
| Conductor - Copper Str Size Range    | 500 / 550 kcmil |
| Conductor - Copper Flex H Size B     | 500 kcmil       |
| Conductor - Copper Flex H Size Range | 500 / 550 kcmil |
| Conductor - Copper Flex I Size A     | 500 kcmil       |

## Configuration

|                |                      |
|----------------|----------------------|
| Connector Type | STANDARD BARREL KITS |
|----------------|----------------------|

## Current

|                   |       |
|-------------------|-------|
| Voltage Rating    | 35 kV |
| Voltage - Maximum | 35000 |

## Dimensions

|                                 |           |
|---------------------------------|-----------|
| Package Height                  | 0.000 in  |
| Package Weight                  | 0.000 lb. |
| Package Length                  | 0.000 in  |
| Package Width                   | 0.000 in  |
| Dimension - L Length Overall mm | 109.22 mm |
| Dimension - Strip Length inch   | 1.77      |
| Dimension - B Length inch       | 1.77 in   |
| Dimension - Length BB inch      | 1.77 in   |
| Dimension - Length Overall inch | 4.3 in    |

## General

|                        |          |
|------------------------|----------|
| Trade Name             | HYLINK™  |
| Die Index              | L99      |
| Die Index Run Side     | L99      |
| Die Index Tap Side     | L99      |
| Feature - Barrel Type  | Standard |
| Feature - Barrel Style | Skived   |

|                     |                      |
|---------------------|----------------------|
| Plated              | Y                    |
| Color Code          | Pink                 |
| UPC                 | 781810343999         |
| Color Code - Side B | Pink                 |
| Color Code - Side A | Pink                 |
| Material            | Copper               |
| Plating Type        | Tin - Electro Plated |
| Finish Type         | Tin-Plated           |
| UPC 12 Digit        | 781810343999         |
| UPC 14 Digit GTIN   | 00781810343999       |

Logistics

|                       |     |
|-----------------------|-----|
| Minimum Pack Quantity | 1   |
| Pallet Quantity       | 900 |
| Carton Quantity       | 10  |

Operational

|                    |     |
|--------------------|-----|
| Temperature Rating | 194 |
|--------------------|-----|

Product Assets

[Catalog \[English\]](#)



A Hubbell brand