



YS38L, Compression Splice, 700 kcmil Cu, Standard Barrel

By Burndy
Catalog # [YS38L](#)

700 kcmil, CU, Standard Barrel SPLICE



Features

- Copper seamless barrel with center stop indentations to indicate when wire is fully inserted into each side of the barrel
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str	700
Compact Size	
Conductor Size	700 KCMIL
Conductor - Material	COPPER
Wire Size	700 kcmil
Conductor Type	CODE
Conductor - Copper Str Size Range	700 kcmil
Conductor - Copper Str Size	700 kcmil

Configuration

Connector Type	STANDARD BARREL
----------------	-----------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	1-3/8 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	82 mm
Dimension - B Length inch	1.38 in
Dimension - Length Overall inch	3.22 in
Dimension - Strip Length inch	1-7/16

General

Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Pink
Trade Name	HYLINK™
Die Index	400
UPC	781810035672
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810035672
UPC 14 Digit GTIN	00781810035672

Logistics

Minimum Pack Quantity	6
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)



A Hubbell brand