



Compression Splice

By Burndy
Catalog # [YS38LFX](#)

500 KCMIL H,I,K, 550 KCMIL G,H,I, 535 DLO, 500 AWG CU,
Standard Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up
to 35kV, PINK Color Code, L99 Die Index.

Features

- Copper Compression Splice
- Standard Barrel with Internal Chamfer

Application

Wire Splice

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	NO
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - CSA Approved	CSA

Conductor

Conductor - Copper Flex G Size	600 KCMIL
Conductor - Copper DLO Size	535 KCMIL
Range	
Conductor - Copper DLO Size	535 KCMIL
Conductor Size	500-550 KCMIL
Conductor - Copper Flex H Size	500-550 KCMIL
Conductor - Copper Flex G Size	550 KCMIL
Range	
Conductor - Material	COPPER
Wire Size	500-550 KCMIL
Conductor - Copper Flex K Size	500 KCMIL
Range	
Conductor - Copper Flex K Size	500 KCMIL
Conductor Type	FLEX
Conductor - Copper Str Size	500-550 KCMIL

Conductor - Copper Flex H Size	500 - 550 KCMIL
Range	
Conductor - Copper Flex I Size	500-550 KCMIL
Conductor - Copper Flex I Size	500 - 550 KCMIL
Range	

Configuration

Connector Type	STANDARD BARREL
----------------	-----------------

Current

Voltage Rating	35 kV
----------------	-------

Dimensions

Length	3.22 in
Dimension - B Length inch	1.31

General

Color Code	Pink
Trade Name	HYLINK™
Sub Brand	HYLINK
Die Index	L99
UPC	621945624016
Type	YS
Construction Material - Main	Copper
Material	COPPER
Finish Type	Tin-Plated

Logistics

Carton Quantity	6
-----------------	---

Product Assets

[Catalog \[English\]](#)