



YS39AT, Aluminum - Compression Splice

By Burndy
Catalog # YS39AT

High Voltage Uninsulated Al Tube Compression Splice, 700/750
kcmil Al Cable, 8.57" L

Features

- Aluminum Compression Splice
- High Voltage Uninsulated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 700 kcmil • 715 kcmil • 750 kcmil
Conductor - AL Str Size Range	700 kcmil-750 kcmil

Configuration

Physical Attribute - Number of Crimps Required	6
Connector Type	Splice

Dimensions

Dimension - Pad Width inch	4.18 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in

Package Width	0.000 in
Dimension - L Length Overall mm	218 mm
Dimension - B Length inch	3.69 in
Dimension - Outside Diameter inch	1.60 in
Dimension - Length Overall inch	8.57 in
Dimension - Strip Length inch	4 1/2

General

Feature - Barrel Type	Standard
Feature - Barrel Style	Tapered
Plated	Y
Color Code	Red
Trade Name	HYLINK™
Die Index	301
UPC	781810001424
Material	Aluminum
Plating Type	Tin - Electro Plated
UPC 14 Digit GTIN	00781810001424

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1440
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)