



YS39LTCKITC, Compression Splice Kit with Clear Heat Shrink, 750 kcmil Cu

By Burndy
Catalog # [YS39LTCKITC](#)

750 kcmil, CU, SPLICE KIT with Clear Heat Shrink



Features

- In-line splice kit includes compression splice connector and heat shrink
- Barrel is designed with internal chamfer at the wire entry to ensure smooth insertion of wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Splice

Specifications

Standards - RoHS Compliance	CM
Status	
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)

Conductor

Conductor Size	750 KCMIL
Conductor - Copper Str Size B	750
Conductor - Material	COPPER
Wire Size	750 KCMIL
Conductor Type	CODE
Conductor - Copper Str Size Range	750 kcmil
Conductor - Copper Str Size	750 KCMIL

Configuration

Connector Type	STANDARD BARREL KITS
----------------	----------------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	104.9 mm
Dimension - B Length inch	1.67 in
Dimension - Length BB inch	1.67 in
Dimension - Length Overall	4.13 in
Dimension - Strip Length inch	1.67

General

Feature - Barrel Type	Standard
Feature - Barrel Style	Skived
Plated	Y
Color Code	Black
Trade Name	HYLINK™
Die Index	24
Die Index Run Side	24
UPC	781810344194
Color Code - Side B	Black
Die Index Tap Side	24
Color Code - Side A	Black
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810344194
UPC 14 Digit GTIN	00781810344194

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1440
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)