



Compression Splice

By Burndy
Catalog # [YS40FX](#)

650 KCMIL G, 646 DLO, 650 AWG CU, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, BLACK Color Code, 24 Die Index.



Features

- Copper Compression Splice
- Long Barrel with Internal Chamfer

Application

Wire Splice

Specifications

Buy American Compliant Certification - cULus	Contact Manufacturer NO
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - CSA Approved	CSA

Conductor

Conductor - Copper Flex G Size	650 KCMIL
Conductor - Copper DLO Size	646 KCMIL
Conductor - Copper DLO Size	646 KCMIL
Conductor Size	650 KCMIL
Conductor - Copper Flex G Size	650 KCMIL
Conductor - Material	COPPER
Wire Size	650 KCMIL
Conductor Type	FLEX
Conductor - Copper Str Size	650 KCMIL

Configuration

Connector Type	LONG BARREL
----------------	-------------

Current

Voltage Rating	35 kV
----------------	-------

Dimensions

Length	6.38 in
Dimension - B Length inch	2.87

General

Color Code	Black
Trade Name	HYLINK™
Sub Brand	HYLINK
Die Index	24
UPC	621945624184
Type	YS
Construction Material - Main Material	Copper COPPER
Finish Type	Tin-Plated

Logistics

Pallet Quantity	1440
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)