



Compression Splice

By Burndy
Catalog # [YS40LFX](#)

650 KCMIL G, 646 DLO, 650 AWG CU, Standard Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, BLACK Color Code, 24 Die Index.

Features

- Copper Compression Splice
- Standard Barrel with Internal Chamfer

Application

Wire Splice

Specifications

Buy American Compliant Certification - cULus	Contact Manufacturer NO
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - CSA Approved	CSA

Conductor

Conductor - Copper Flex G Size	650 KCMIL
Conductor - Copper DLO Size Range	646 KCMIL
Conductor - Copper DLO Size	646 KCMIL
Conductor Size	650 KCMIL
Conductor - Copper Flex G Size Range	650 KCMIL
Conductor - Material	COPPER
Wire Size	650 KCMIL
Conductor Type	FLEX
Conductor - Copper Str Size	650 KCMIL

Configuration

Connector Type	STANDARD BARREL
----------------	-----------------

Current

Voltage Rating	35 kV
----------------	-------

Dimensions

Length	3.75 in
Dimension - B Length inch	1.56

General

Color Code	Black
Trade Name	HYLINK™
Sub Brand	HYLINK
Die Index	24
UPC	621945623880
Type	YS
Construction Material - Main Material	Copper COPPER
Finish Type	Tin-Plated

Logistics

Pallet Quantity	3000
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)